



1. Interface Connection (High Speed Wire-to-Board)

Noise Resistant

105°C

**GT43**

Compact,
One Step Crimping
Frequency: 3GHz
Coaxial Cable: 1.5D

High Speed

105°C

**GT32**

Transmission Rate:
4pos.: USB2.0, LVDS Equivalent
10pos.: USB3.2 Gen.1 Equivalent
19pos.: HDMI 1.4a Type E Equivalent
AWG: 24-28
Cable Type: Twist

USB Type-C

105°C

**AU1**

USB 3.2 Gen2 (10Gbps),
Display Port 1.4, HDMI
Rated Current: 5A Max.
Compliant with USCAR-2 and
USCAR-30 standards

2. Internal Connection (Wire-to-Board)

**GT50**

Rated Current:
1.5A (6-16pos.)
2.0A (2,4pos.)
No. of Pos.: 2-16
AWG: 28

**ZE05**

Rated Current: 2A
(All Pins Power Supply)
No. of Pos.: 2-24
AWG: 20-26

**GT25**

Rated Current: 3A
(All pins Power Supply)
No. of Pos.: 8-40
AWG: 20-26

**KM32A**

Rated Current: 5A
No. of Pos.: 2-10
AWG: 20

**FX23/FX23L**

PCIe Gen.4 (16Gbps)
Pitch: 0.5mm
Stacking Height:
8.0-30.0mm

**BM54**

Compact
Pitch: 0.4mm
Stacking Height:
3.0-4.5mm

**DF40T**

Low Profile,
Narrow Pitch: 0.4mm
Stacking Height: 1.5-7.0mm
1.5 (Shielded Type: DF40GT)

**DF12N**

Space-saving Design
Pitch: 0.5mm
Stacking Height:
3-5mm

3. Internal Connection (FPC/FFC, FPC-to-Board)

Best Selling



FH75/FH75M
FH™
Two-point Contact
Pitch: 0.5/0.4mm
Height: 2.0mm
FH75M: 100pos.



FH52K
FH™
Pitch: 0.5/1.0mm
Height: 2.0mm



FH79
FH™
Pitch: 0.3mm.
Height: 1.2mm



FH63S/FH67
FH™
One Action
105°C
Pitch: 0.5mm
Height: 2.8, 5.2mm

Top/Bottom Contact



FH69
FH™
Independent
Two-Point Contact
Pitch: 0.5mm
Height: 2.3mm



FH65
FH™
Low Profile,
Space-saving Design
Pitch: 0.5mm
Height: 1.2mm



FH41
FH™
Low Profile,
Space-saving Design
Pitch: 0.5mm
Height: 2.5mm



FH48
FH™
Low Profile,
Space-saving Design
Pitch: 0.5mm
Height: 6.18mm



ZK1
FH™
Vertical Connection
Pitch: 2mm
Rated Current: 1A
No. of Pos.: 32