


# HVAC Systems


[Click here to request a sample](#)

## Control box(sealed)

## Fan



**DF63**  
Positive Lock  
Rated Current : 15A Max.  
Rated Voltage : 630V AC/DC  
Pitch : 3.96mm  
No. of Pos. : 1-6  
AWG : 16-22



**DF22**  
Rated Current : 30A Max.  
Rated Voltage : 1000V AC/DC  
Pitch : 7.92mm  
No. of Pos. : 1-5  
AWG : 10-16



**DF60**  
Rated Current : 65A Max.  
Rated Voltage : 1000V AC/DC  
Pitch : 10.16mm  
No. of Pos. : 1-6  
AWG : 8-12



## Compressor

## Contactor/Capacitor

## Power connection



**HVH-280 (Waterproof) Series**  
High Voltage/Power Supply  
Compact Waterproof Design  
120°C Heat Resistance  
30A Max



**BH12 Series**  
IPX6/IPX7 Waterproof  
Light Weight  
**Power/Signal Hybrid**  
20A Max.



**DF63W Series**  
IP67 Waterproof  
(When Mated)  
Rated Current : 14A Max.  
Rated Voltage : 630V AC/DC  
Pitch : 3.96 x 4.4mm  
No. of Pos. : 2-5  
AWG : 16-22



## Signal connection



**DF62W Series**  
IP67 Equivalent  
(When Mated)  
Rated Current : 5A Max.  
Rated Voltage : 250V AC/DC  
Pitch : 2.0 x 2.2mm  
No. of Pos. : 2-4, 6, 9  
AWG : 20-26



**HR34P Series**  
IPX7, IPX8 Waterproof  
Rated Current: 3A  
No. of Pos.: 10  
AWG: 20-25



**ZE064W Series**  
0.64mm Terminal  
Tab Size  
125°C Heat  
Resistance



**HR30 Series**  
IP67/IP68 Waterproof  
(When Mated)  
Rated Current: 5A Max.  
(6, 10, 12pos.: 2A Max.)  
No. of Pos. : 3, 6, 10, 12  
AWG: 26-30 (3pos.: 20)



**LF Series**  
IP67/IP68 Waterproof  
(When Mated)  
Rated Current : 10A Max.  
No. of Pos. : 3, 4, 6, 11, 12, 20  
AWG : 16-26