


UPS


Fan and control board

P=2.0mm, AWG22-30, Wire to Board connector


DF11 Series
Friction lock



DF51 Series
Side lock



DF51 K Series
Center lock





P=2.2mm, AWG20-26, IP67 connector

DF62 Series
Non IP rated



DF62W Series
IP67 rated



Straight type
Vertical mating?
Friction lock is fine?
AWG18-26??
Pig tail to a board