


4. Battery Unit



4. Battery Unit

Wire-to-Board

**DF63**

In-Line Type Available
Pitch : 3.96/7.92mm
Rated Current : 15.0A Max.

**DF59M**

Low Profile 1pos.
Rated Current : 6.0A Max.

Board-to-Board

**FX30B**


Pitch : 3.81/7.62mm
Height : 20.0-30.0mm
11.0mm (Coplanar, Right Angle)
Rated Current : 25.0A Max.

Waterproof

**HR30**

IPX7, IPX8 Waterproof
Rated Current : 5.0A Max.

FPC/FFC

**FH52K**

Pitch : 0.5/1.0mm
Height : 2.0mm
Depth : 5.7mm
Rated Current : 0.5A

**FH34**

Pitch : 0.5mm
Height : 1.0mm
Depth : 3.8mm
Rated Current : 0.5A

**FH62/FH72**

Pitch : 0.25/0.3mm
Height : 1.1/0.9mm
Depth : 4.0/3.5mm
Rated Current : 0.3A

**FH63S**

Pitch : 0.5mm
Height : 2.8mm
Depth : 5.15mm
Rated Current : 0.5A