# **Industrial Sensors**

# Pressure Sensor with Digital Interface and Display



In-line

## **Interface**

### Without Shielding



#### **HR10**

Rated Current: 2A Max. No. of Pos.: 7, 10, 13 AWG: 26-30



#### **HR30**

IPX7/IPX8 Waterproof Rated Current: 5A Max. No. of Pos.: 3, 6, 10, 12 AWG: 26-30



**With Shielding** 

#### LF

IPX7/IPX8 Waterproof Compact, Rugged Bayonet Lock EMI Prevention No. of Pos.: 3-20



#### IX

IEC Standard Product Compact, Rugged I/O Connector Supports Cat.6A Ethernet

FH63S/FH67

## **Internal Connection**

#### **Board-to-Board**



#### **DF40**

USB4 Gen.2 (10Gbps) Pitch: 0.4mm Stacking Height: 1.5-4.0mm No. of Pos.: 10-120



#### Function MAX. FX23/FX23L

16Gbps High Speed Pitch: 0.5mm No. of Pos.: 2-120 Stacking Height: 15-30mm

## FFC/FPC



#### **FH34**

Backflip Pitch: 0.5mm Height: 1.0mm No. of Pos.: 4-50



#### FH41/FH48

Noise Prevention (Shield FFC) Pitch: 0.5mm Height: 2.5mm (FH41) 6.18mm (FH48) No. of Pos.: 15-68

m Pitch: 0.5mm mm (FH41) Height: 2.8mm (FH63S) mm (FH48) 5.2mm (FH67)

Signal Bee

5.2mm (FH67) No. of Pos.: 10, 20, 30, 40

Simply Insert to Connect

OneAction FH.

## In-line (Wire-to-Wire)



#### **DF62**

Rated Current: 4A Max. Pitch: 2.0 x 2.2mm No. of Pos.: 2-7, 13, 24 AWG: 22-30



#### **DF51**

Rated Current: 3A Max. Pitch: 2.0mm No. of Pos.: 2-30 AWG: 22-30



## EnerBee

# DF63W

IP67 Waterproof (Mated) Rated Current: 14A Max. Pitch: 3.96mm No. of Pos.: 2, 3, 4 AWG: 16-22



## DF62W

IP67 Equivalent (Mated) Rated Current: 5A Max. Pitch: 2.0 x 2.2mm No. of Pos.: 2, 3, 4, 6, 9 AWG: 20-26





## SignalBee 🕏

KW30 Rated Current: 3A Max. Pitch: 1.0mm No. of Pos.: 2-15

AWG: 28-30

## **DF51/DF51K**

Side or Center Lock Rated Current: 3A Max. Pitch: 2.0mm No. of Pos.: 2-30 AWG: 22-30



#### **DF52**

Rated Current: 2.5A Max. Pitch: 0.8mm No. of Pos.: 2-20 AWG: 28-32

