


Solutions for Scalability/Modularity

Floating / Blind-Mate Structure


Busbar option



FX31 Series

Pitch: 9.5 mm
Height: 20 mm


25A.Max, up to 50pos



FX30B Series


Pitch: 3.81 / 7.62 mm
Height: 20 - 30 mm

High speed




FX18 Series


Pitch: 0.8 mm
Height: 10 - 45 mm



Reduction of Cable Usage – Branch Adaptor Family -




Wide Variation



DF51 Series

Pitch: 2.0 mm
AWG20-30

30A



DF22 Series

Pitch: 7.92 mm
AWG10-16

Space saving

L-shape plug



DF60 Series

Pitch: 10.16 mm
AWG8-12, 65A

Network Communication

Industrial Ethernet



IX Series

Rugged compact I/O
Up to 10 Gbps, IP54/IP67

USB type-C



CX Series

USB Type-C
High-speed data (20Gbps)