



5. Drive Unit (Front/Center/Rear Motor)

Wire-to-Board



DF63

In-Line Type Available
Pitch : 3.96/7.92mm
Rated Current :
15.0A Max.

High Vibration
Resistance
125°C

ZE05

Pitch : 2.0mm:
Rated Current :
5.0A Max.

High Vibration
Resistance
125°C

GT50

Pitch : 1.0mm
Rated Current :
2.0A Max.

Board-to-Board



FX23/FX23L

Pitch : 0.5mm
Height : 8.0-30.0mm
Rated Current :
3.0A (Power)
0.5A (Signal)

FPC/FFC



FH67

Pitch : 0.5mm
Height : 5.2mm
Depth : 3.57mm
Rated Current : 0.5A

Waterproof



BH12

IPX6/IPX7 Waterproof
Power Hybrid
Rated Current :
20.0A (Power)
1.0A (Signal)

Push-Pull



HR30

IPX7, IPX8 Waterproof
Rated Current :
5.0A Max.



DF62W

For Signal
IP67 Equivalent
Pitch : 2.2mm
Rated Current :
5.0A Max.



DF63W

IP67 Waterproof
Pitch : 3.96mm
Rated Current : 14.0A Max.