


Connectors For Automotive Camera



Click here to request a sample



1. Internal Connection (Floating Board-to-Board, Board-to-Board (FPC))




Floating Design
125°C

BM54
Floating, Compact
Pitch : 0.4mm
Stacking Height : 3.0-4.5mm



125°C


DF40T
Low Profile,
Narrow Pitch : 0.4mm Stacking
Height : 1.5-7.0mm
1.5 (Shielded Type : DF40GT)



105°C


DF12N
Space-saving Design
Pitch : 0.5mm
Stacking Height : 3-5mm

2. Internal Connection (FPC/FFC)



125°C

FH75/FH75M
Pitch : 0.4/0.5mm
Front Flip
Two-Point Contact




125°C

FH52K
Pitch : 0.5/1.0mm
Height : 2.0mm
Best Selling



125°C
One Action

FH63S
Horizontal Connection
Pitch : 0.5mm Height :
2.8mm



125°C
One Action

FH67
Vertical Connection
Pitch : 0.5mm Height
: 5.2mm



125°C


FH69
Back Flip, Independent
Two-Point Contact
Pitch : 0.5mm
Height : 2.3mm



125°C

FH65
Low Profile,
Space-saving Design
Pitch : 0.5mm Height
: 1.2mm

3. Interface Connection (High speed Wire-to-board, Wire-to-board)



Noise Resistant
105°C

GT43
Compact, One Step Crimping
Frequency : 3GHz
Coaxial Cable : 1.5D



Robust
125°C


ZE05
Pitch : 2mm
Rated Current :
2A (All pins power supply)
No. of Pos. : 2-24 AWG : 20-22



105°C


GT25
Pitch : 2.2mm
Rated Current :
3A (All pins power supply)
No. of Pos. : 8-40
AWG : 20-26

4. Internal Connection (Coaxial)




105°C

POK15
Wire-to-Board
Mated Height : 14mm
V.S.W.R. :
1.5 Max. (0 to 3GHz)



105°C

POK16
Board-to-Board
Mated Height :
7.4mm
V.S.W.R. :
1.5 Max. (0 to 3GHz)



105°C

POK19
Board-to-Board,
Wire-to-Board
Mated Height : 9, 12mm
V.S.W.R. :
1.5 Max. (0 to 6GHz)



105°C

POK22
Floating
Mated Height : 16.45mm
V.S.W.R. :
1.49 Max. (0 to 6GHz)