

Refrigeration for Trailer

1. Waterproof (IP67) Inline connector



Slim & Compact

DF62W/DF63W Series

P=2.2mm/3.96mm, AWG16-26



2. Branch family



Clean Cable routing

DF22/DF51 Series

P=7.92mm/2.0mm, AWG10-30, 30A/pin.max



2. For Power Supply

X,Y,Z floating



FX31 Series

P=9.5mm, 25A/pin

20A/pin+1A/pin




BH12 Series

IPX6/IPX7, AWG14 (20A/pin)

2. For Battery Monitoring System

Rugged FPC/FFC



TB4 Series

P=1.0mm, H=4.5mm

Vibration Resistance



KW30 Series

P=1.0mm, AWG28-32

2. For Controller

Top & Bottom contact



FH34 Series

P=0.5mm, H=1.0mm

High HT & Vib resistance



DF40T Series

P=0.4mm, H=1.5-7.0mm