


Wire-to-Board Connector



Battery

Waterproof Connector,
Interface Connector

2. Controller / Shift Lever


4. Battery Unit

1. Cycle Computer
(Display/Battery)3. Front/Center/Rear Unit
(Speed Sensor, Torque Sensor)5. Drive Unit
(Rear Motor)5. Drive Unit
(Center Motor)5. Drive Unit
(Front Motor)

2. Controller / Shift Lever

Wire-to-Board


SignalBee

**DF13**Height : 5.8mm Max.
Pitch : 1.25mm
Rated Current : 2.5A Max.

SnapBee

For Battery
Low Profile
Swing Lock**DF57**Pitch : 1.2mm
Height : 1.4mm
Depth : 4.65mm
Rated Current : 3.0A Max.

SnapBee

For Battery
Low Profile
ViSe Lock**DF58**Pitch : 1.2mm
Height : 1.0mm
Depth : 4.97mm
Rated Current : 3.0A Max.

Waterproof

Interface

Push-Pull

**HR30**IPX7, IPX8 Waterproof
Rated Current : 5.0A Max.CX
series**CX**USB Type-C™
Waterproof Type Available