



FPC/FFC Connector



3. Front/Center/Rear Unit (Speed Sensor, Torque Sensor)


Wire-to-Board



For Battery
Low Profile
Swing Lock

DF57

Pitch : 1.2mm
Height : 1.4mm
Depth : 4.65mm
Rated Current : 3.0A Max.




For Battery
Low Profile
ViSe Lock

DF58

Pitch : 1.2mm
Height : 1.0mm
Depth : 4.97mm
Rated Current : 3.0A Max.

FPC/FFC



TOP & Bottom Contact
Backflip

FH34

Pitch : 0.5mm
Height : 1.0mm
Depth : 3.8mm
Rated Current : 0.5A



OneAction Lock
For Display

FH62/FH72

Pitch : 0.25/0.3mm
Height : 1.1/0.9mm
Depth : 4.0/3.5mm
Rated Current : 0.3A