

Applications



Industrial Robot



Medical Equipment



Manufacturing Equipment



Positive-Lock



Power Supply



Wide Variation

Introducing Hirose's DF22B Series—a compact branch adapter engineered for high-current power distribution. With a 7.92 mm pitch and rated up to 30 A/contact at 1000 V AC/DC, the DF22B reduces wire usage and routing space, shortens wiring length, and streamlines panel layouts—helping lower overall system cost.

Available in standard (cable-tie) and flange/screw versions for secure mounting, the DF22B uses crimp terminations for strong electrical and mechanical performance. UL/C-UL/TÜV approved, it supports 50 mating cycles and operates from -55°C to +85°C, making it ideal for semiconductor tools, robots, conveyors, mounting equipment, and service robots.


KEY BENEFITS OF THE DF22B SERIES INCLUDE:

- Rated up to 30 A/contact at 1000 V AC/DC for compact, high-current branching.
- 7.92 mm pitch adapter housing reduces wiring complexity and cost.
- Branch adapter design minimizes wiring length and routing space, lowering overall system cost.
- Two options: standard (cable-tie mounting) and flange/screw type for secure panel or housing attachment.
- Crimp terminations provide strong electrical and mechanical performance—no soldering required.
- UL, C-UL & TÜV safety compliance; 50 mating cycles; -55 °C to +85 °C operating range



Dimensions

**Single-row,
Ex: 2pos.**



**CLICK HERE
FOR MORE INFORMATION**

**CLICK HERE TO ORDER
SAMPLE NUMBER:
US-DF22BSAMPLE-25**

Combination Example



Socket	DF22-2S-7.92
Retainer	DF22-2RS/P-7.92
Header	DF22-2P-7.92DSA
B: when using High Profile type	C: when using Enhanced ergonomic lock

Socket	DF22-2S-7.92
Retainer	DF22-2RS/P-7.92
Header	DF22-2P-7.92DS
B: when using High Profile type	C: when using Enhanced ergonomic lock

Socket	DF22-2S-7.92
Retainer	DF22-2RS/P-7.92
In-line Plug	DF22A-2EP-7.92C
Retainer	DF22B/C-2RS/P-7.92

Branch Socket	DF22S-2S-7.92C
Branch Adapter	DF22BA-2EP-7.92A-3PRT
	B: when using Flange Type
	*Branch socket does not require a retainer.

Many Varieties



*Non-branching DF22 has three keyings / color options, and type with larger lock for enhanced operability is also available.

Specifications

Material and Finish

COMPONENT		MATERIAL		FINISH, REMARKS	
Socket	Insulator	Polyamide			Natural (Beige) / Black / Red, UL94V-0
Crimp Contact	Contact	Highly Conductive Copper Alloy			Gold Plating
Header	Insulator	Polyamide (Glass Reinforced)			Natural (Beige) / Black / Red, UL94V-0
	Contact	Highly Conductive Copper Alloy			Gold Plating
Adapter	Insulator	Polyamide (Glass Reinforced)			Black, UL94V-0
	Contact	Highly Conductive Copper Alloy			Gold Plating

Performance Characteristics

Rated Current* ¹	Pos.	10 AWG	12 AWG	14 AWG	16 AWG
	1	30A	25A	20A	15A
	2,3	25A	20A	18A	15A
	4,5	22A	18A	15A	13A
Rated Voltage		1,000V AC/DC (UL approved at 600V)			
Operating Temperature		-55 to +85°C* ²			
Contact Resistance		5mΩ Max. (20mV Max., 1mA)			
Withstand Voltage		2,500V AC for 1 min.			
Insulation Resistance		1,000MΩ Min. (1,000V DC)			
Mating Durability		30 mating cycles			

-Variations: Single-row 1-5pos., Double-row (In-line) 4pos., Branch 2, 3pos.
-RoHS Compliant

*¹: For a branch adapter supports up to 30A when using 10 AWG.

*²: Includes the temperature rise due to current flow.



For additional information please go to
www.hirose.com/product/series/DF22

Specifications herein are subject to change without notice.
Contact Hirose for latest specifications, drawings, or availabilities.

STAY CONNECTED

