

1. Internal Connection (FPC/FFC)

125°C

**FH75/FH75M FH**

Two-point Contact
Pitch: 0.5/0.4mm
Height: 2.0mm
FH75M: 100pos.

Best Selling

125°C

**FH52K FH**

Pitch: 0.5/1.0mm
Height: 2.0mm

Top/Bottom Contact


125°C

**FH79 FH**

Pitch: 0.3mm.
Height: 1.2mm

One Action

105°C

**FH63S/FH67 FH**

Pitch: 0.5mm
Height: 2.8, 5.2mm

Top/Bottom Contact

125°C

**FH69 FH**

Independent
Two-Point Contact
Pitch: 0.5mm
Height: 2.3mm

1. Internal Connection (FPC/FFC)

125°C

**FH65 FH**

Low Profile,
Space-saving Design
Pitch: 0.5mm
Height: 1.2mm


Robust

125°C

**FH28K FH**

Pitch: 0.5/1.0mm
Height: 2.55mm

105°C

**FH40 FH**


Vertical Connection
Pitch: 0.5mm
Height: 5.8mm

105°C

**FH41 FH**

Shielded FFC
Pitch: 0.5mm
Height: 2.5mm


85°C

**FH48 FH**

Vertical Connection
Shielded FFC
Pitch: 0.5mm
Height: 6.18mm


Floating Design

125°C

**BM54**


Compact
Pitch: 0.4mm
Stacking Height:
3.0-4.5mm

125°C

**DF40T**

Low Profile,
Narrow Pitch: 0.4mm
Stacking Height: 1.5-7.0mm
1.5 (Shielded Type: DF40GT)

105°C

**DF12N**

Space-saving Design
Pitch: 0.5mm
Stacking Height: 3-5mm

1. Internal Connection (Coaxial, Wire-to-Board)

105°C

**POK15**

Wire-to-Board
Mated Height:
14mm
V.S.W.R.:
1.5 Max. (0 to 3GHz)

105°C

**POK16**

Board-to-Board
Mated Height:
7.4mm
V.S.W.R.:
1.5 Max. (0 to 3GHz)

105°C

**POK19**

Board-to-Board,
Wire-to-Board
Mated Height:
9, 12mm
V.S.W.R.:
1.5 Max. (0 to 6GHz)


125°C

**GT50**

Rated Current:
1.5A (6-16pos.)
2.0A (2,4pos.)
No. of Pos.: 2-16
AWG: 28

Noise Resistant

105°C

**GT43**

Compact,
One Step Crimping
Frequency: 3GHz
Coaxial Cable: 1.5D

High Speed

105°C

**GT32**

Transmission Rate:
4pos.: USB2.0, LVDS
Equivalent
10pos.: USB3.2 Gen.1
Equivalent
19pos.: HDMI 1.4a Type E
Equivalent
AWG: 24-28
Cable Type: Twist

USB Type-C

105°C

**AU1**

USB 3.2 Gen2 (10Gbps),
Display Port 1.4, HDMI
Rated Current: 5A Max.
Compliant with
USCAR-2 and USCAR-30
standards


Robust

125°C

**ZE05**

Rated Current: 2A
(All Pins Power Supply)
No. of Pos.: 2-24
AWG: 20-26

125°C

**KM32A**

Rated Current: 5A
No. of Pos.: 2-10
AWG: 20

2. Interface Connection (High Speed Wire-to-Board, Wire-to-Board)