

Power Infrastructure HMI (Display, Buttons, etc.)

[Click here to request a sample](#)


Low profile



FH34 Series

Pitch: 0.5 mm
Height: 1.0 mm

Front Flip FPC/FFC



TF31 Series

Pitch: 0.5 / 1.0 mm
Height: 1.75 / 2.0 mm

Vertical FPC/FFC



TF38 Series

Pitch: 0.5 mm
Height: 5.2 mm, 0.5 A


One insertion Step



FH63S Series

Pitch: 0.5 mm
Height: 2.8mm

Rugged, wide variation



HIF3M*W Series

Pitch: 2.54 mm
AWG28, Wire to Board

Positive lock




DF51K Series

Pitch: 2.0 mm
AWG22-30


High Retention

Lock Contact Securely holds FPC tab



Automation process

Visual Inspection window



Clear Tactile Click

